



FRONT VIEW

- ① INTELLISLOT PORT. NETWORK COMMUNICATIONS CARD OPTIONAL
- ② 13A INPUT CIRCUIT BREAKER
- ③ INPUT POWER CORD: NEMA 5-15P WITH 10 FOOT ATTACHED CORD
- ④ EPO CONNECTOR
- ⑤ USB PORT
- ⑥ OUTPUT RECEPTACLES: 2 NEMA 5-15R PROGRAMMABLE GROUP
- ⑦ OUTPUT RECEPTACLES: 3 NEMA 5-15R ALWAYS ON
- ⑧ ON/MUTE BUTTON
- ⑨ SELECT BUTTON
- ⑩ OFF/ENTER BUTTON



REAR VIEW



SIDE VIEW

- NOTES:
1. UNIT DIMENSIONS: 17.2" x 20.1" x 1.7" (438mm) x (511mm) x (44mm)
  2. UNIT WEIGHT: 36.4LBS (16.5KG)
  3. SHIPPING DIMENSIONS: 22.1" x 23.4" x 5.5" (540mm) x (595mm) x (140mm)
  4. SHIPPING WEIGHT: 40.8LBS (18.5KG)
  5. MINIMUM AIRFLOW CLEARANCE IS 4.0" (100.0mm) - FRONT/REAR
  6. FIXED RAIL KIT: INCLUDED.
  7. ALL SITE WIRING IS TO BE IN COMPLIANCE WITH NATIONAL AND LOCAL ELECTRIC CODES
  8. UNIT INPUT: 100~125 VAC, 60/50HZ, 13A
  9. UNIT OUTPUT: 100/110/115/120/125VAC, 60/50HZ, 1000VA/900W, 8A, @125VAC INPUT OR 1000VA/900W, 8.3A, @120VAC INPUT OR 1000VA/900W, 8.7A, @115VAC INPUT OR 850VA/765W, 7.7A, @110VAC INPUT OR 850VA/765W, 8.5A, @100VAC INPUT

DRAWN BY B. LAY CHK BY L. JOHNSON REF. DWG.	SHEET NO. 1 OF 1 ECN NO. ORDER NO.	PS15-1000RM1201U	DWG. NO. PS15-1000RM1201U DATE 10-14-19 REV. # 0	1050 DEARBORN DRIVE P.O. BOX 29186 COLUMBUS, OHIO 43229	
---	---	------------------	---	---	--