





REAR VIEW



SIDE VIEW



FRONT VIEW



#10-32 BLIND PEM NUT
(REQUIRED FOR TOOLLESS MOUNTING)
3 PLACES

19.1mm
[0.75in]

50.8mm
[2.00in]

50.8mm
[2.00in]

AGENCY COMPLIANCE:
UL & c-UL Listed 60950
RoHS Compliant
FCC Part 15 Class A Conformance

ENVIRONMENTAL RATING:
Maximum Operating Temperature: 60C / 140F

NOTES
UNIT DIMENSIONS: 66.25in x 2.0in x 2.0in / 1683mm x 51mm x 51mm
SHIPPED WEIGHT: 15lbs (6.80kg)
SHIPPING DIMENSIONS: 72in x 9in x 7in / 1829mm x 223mm x 159mm
Toolless Mounting Hardware 61.25in / 1556mm and 64.75in / 1645mm, and 7938 Vertical Mounting Bracket Kit

OUTPUT POWER

CIRCUIT	PHASE	RECEPTACLE TYPE (QUANTITY)	VOLTAGE (V)	MAX. CONTINUOUS AMPS (A)	
				PER RECEPTACLE	PER CIRCUIT
1	L1	24XNEMA 5-20R	100-120	16	16

INPUT POWER

INPUT CORD	INPUT PLUG	WIRE COUNT	FREQUENCY (Hz)	VOLTAGE (V)	RATED AMPS (A)	MAX. CONT. AMPS (A)
10 FT	NEMA L5-20P	1/N/PE	50/60 Hz	100-120V	20	16

METERING PARAMETER	MEASUREMENT ACCURACY
VOLTAGE	±1%
CURRENT	±1% - Input Current ±2% - Circuit/Breaker Current

		Allgemeintoleranzen General tolerances		Oberfläche Finish		Werkstoff / Material		Gewicht: Weight: -	
		-		-		-		-	
Dimensions in mm		Drawn	Date	Name		Bezeichnung / Description			
		Checked	21/06/18	SW		Monitored, Vertical, 20A, 120V, (24)5-20R			
		Approved	-	-					
		Zeichnungs-Nr. / Drawing no.				Maßstab Scale			
		VP8830				1:6			
		Verwendet in / Used in				-		Blatt/Sheet	
		-				-		1/1	
Rev.	Change	Date	Name						

Disclosure and photocopying of this document, exploitation and communication of its contents are not permitted, unless permission is expressly granted. All rights are reserved.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Alle Rechte vorbehalten.